



# **NOTES:**

- MATERIAL AND FINISHES:**  
 INSULATOR: GLASS-FILLED NYLON, UL 94V-0. COLOR: GREEN  
 CONTACTS: PRECISION MACHINED COPPER ALLOY WITH GOLD FLASH OVER NICKEL PLATE.  
 SHORTING CLIP: COPPER ALLOY WITH GOLD PLATE.  
 SWAGED RIVET: COPPER ALLOY WITH GOLD PLATE.
- NOT INTENDED TO BE USED AS A CURRENT INTERRUPT DEVICE.
- CONTACTS ORDERED SEPARATELY.
- CONNECTOR DESIGN ALLOWS MALE CONTACTS TO BE SHORTED ON UNMATING AND MATING SHORTING IS REMOVED.
- DETAILED PRODUCT, MECHANICAL AND ELECTRICAL INFORMATION IS AVAILABLE IN THE LATEST STANDARD AUTOSHUNT PRODUCT PUBLICATION AT [CONNECTPOSITRONIC.COM](http://CONNECTPOSITRONIC.COM).
- CONNECTORS ARE COMPLIANT TO THE CURRENT RoHS DIRECTIVE.

BY NUR		CHK LAW		3RD ANGLE 	POSITRONIC BELIEVES THE DATA ON THE DRAWING TO BE RELIABLE. THE USER EMPLOYS SUCH INFORMATION AT HIS OWN DISCRETION AND RISK. POSITRONIC ASSUMES NO RESPONSIBILITY FOR RESULTS OBTAINED OR DAMAGES INCURRED FROM USE OF SUCH INFORMATION IN WHOLE OR IN PART.	 <b>Positronic®</b> CONNECTPOSITRONIC.COM	
APR PA		RELEASED DATE: 2019-03-01					SCALE NTS
TOLERANCES  ±0.03mm [.001 INCHES]FOR MALE CONTACT MATING DIAMETERS ±0.08mm [.003 INCHES]FOR CONTACT TERMINATION DIAMETERS ±0.13mm [.005 INCHES]FOR ALL OTHER DIAMETERS ±0.38mm [.015 INCHES]FOR ALL OTHER DIMENSIONS ±5° FOR ALL ANGLES DIMENSION ARE IN MILLIMETERS [INCHES]					PART NUMBER DFS02M00/AA		SERIES AUTOSHUNT
TITLE DFS02M00/AA					CREATED ON: 2019-02-05	SHEET SHEET 1 OF 1	REV A