


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	ECN-23-204905:Customer Drawing created	27MAR2023	SM	RB



TECHNICAL DATA / Technische Daten

COLOUR / Farbe:.....BLACK / Schwarz
TEMPERATURE RANGE/ Temperaturbereich.....-30°C to +90°C
HARDNESS / Haerte Shore A DIN ISO 7619-1..... 60-70 SHA


CHEMICAL RESISTANCE / Chemische Bestaendigkeit:

OIL RESISTANCE / OelbestaendigkeitGOOD / gut
PETROL RESISTANCE / Benzinbestaendigkeit.....GOOD / gut
ACID RESISTANCE / SaeurebestaendigkeitVERY GOOD / sehr gut
ALKALI RESISTANCE / LaugenbestaendigkeitVERY GOOD / sehr gut

PACKAGING INSTRUCTIONS / Verpackungsanweisungen

100 PCS IN A BAG / 100 Stueck im Paket

1:1



© 2023 TE Connectivity. All Rights Reserved.

DIMENSIONS: mm	DWN S.MAHAPATRA 27MAR2023	MATERIAL Cr 65+-5 SHORE	FINISH -
TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN ISO 2768 cL	CHK R.BAUMGARTNER - APVD R.BAUMGARTNER - PRODUCT SPEC	 TE Connectivity	
0 PLC ±- 1 PLC ±0.5 2 PLC ±0.13 3 PLC ±0.013 4 PLC ±0.0001 ANGLES ±	APPLICATION SPEC - WEIGHT 0.38 g		
CUSTOMER DRAWING		NAME SEALING RING DICHTRING	RESTRICTED TO -
		SIZE A 4	CAGE CODE 00779
		DRAWING NO C-K1163926-CD	
		SCALE 5:1	SHEET 1 OF 1
		REV A	