



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	07/20/2022	GUTTADAURO




"HOSPITAL GRADE" DESIGNATION



NEMA HG 5-15P
PLUG



SJT 14AWG, BLACK
3-COND CORDAGE



C19 LOCKING
CONNECTOR

TABULATION BLOCK

ITEM NO.	LENGTH ±.6 [15]
C19LHGN515P-15-3F	36.0 [914]
C19LHGN515P-15-6F	72.0 [1829]

NOTES:

1. PLUG: HOSPITAL GRADE NEMA 5-15P, BLACK
2. CONNECTOR: EN60320 C19 LOCKING, BLACK
3. CORDAGE: SJT3X14AWG, BLACK
COLOR CODING OF CONDUCTORS: BLACK, WHITE, GREEN
APPROVALS: UL/CSA
RATING: 15A/125V
4. OPTIONAL LABELS MAY INCLUDE UL, CURRENT AND/OR WARNING.
5. CABLE ASSEMBLIES SHALL BE INDIVIDUALLY PACKAGED.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5] FRACTIONS ± 1/32 .XX = ±.02 [.5] ANGLES ± 1° .XXX = ±.005 [.13] THIRD-ANGLE PROJECTION 	APPROVALS	DATE	 an INFINITI® brand 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY AKRESOWSK	07/20/2022	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	CHECKED BY DGUST	07/20/2022	CATEGORY POWER PRODUCTS
	APPROVED BY GUTTADAURO	07/20/2022	
COLOR VARIATIONS MAY OCCUR	PRODUCT DESCRIPTION IEC LOCK C19 TO HG NEMA 5-15P, 15A, 125V		REV. A
	SIZE A	CAGE CODE 43321	
SCALE: NONE		CAD FILE: C19LHGN515P-15.SLDDRW	SHEET 1 OF 1