



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE
WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	5/11/2023	SREITER	GUTTADAURO



NOTES:

1. PLUG: TYPE C14, BLACK
2. CONNECTOR: C19 LOCKING, BLACK
3. CORDAGE: SJT3X14/H05VVF3G1.5mm², BLACK
4. FOR REFERENCE ONLY:
 - A. COLOR CODING OF CONDUCTORS: BLUE, BROWN, GREEN/YELLOW
 - B. APPROVALS: ENEC, UL, cUL, SAA
 - C. RATING: 15A/250V (U.S.), 10A/250V (EUROPE)
5. OPTIONAL LABELS MAY INCLUDE UL, CURRENT AND/OR WARNING.
6. CABLE ASSEMBLIES SHALL BE INDIVIDUALLY PACKAGED.

TABULATION BLOCK	
ITEM NO.	LENGTH ±.6 [15]
C19LC14-15-3F	36.0 [914]
C19LC14-15-6F	72.0 [1829]
C19LC14-15-10F	120.0 [3048]

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		<div>L-com™</div> <div>an INFINITT® brand</div>		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0		DRAWN BY SREITER		5/11/2023					
		CHECKED BY DGUST		05/11/2023					
		ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]		APPROVED BY GUTTADAURO		05/11/2023		POWER PRODUCTS	
THIRD-ANGLE PROJECTION 		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION					
				IEC LOCK C19 TO C14, 15A, 250V					
		COLOR VARIATIONS MAY OCCUR		SIZE	CAGE CODE	ITEM NO.		REV.	
				A	43321	C19LC14-15		A	
				SCALE: NONE		CAD FILE: C19LC14-15-10F.SLDDRW			SHEET 1 OF 1