


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	08/29/22	GUTTADAURO



C14 PLUG

2.7
[68]

SJT 14AWG/H05VVF3G1.5MM², BLACK
3-COND CORDAGE

3.3
[83]


C19 LOCKING
CONNECTOR

1.3
[33]

TABULATION BLOCK	
ITEM NO.	LENGTH ±.6 [15]
C19LC14-15-3F	36.0 [914]
C19LC14-15-6F	72.0 [1829]

NOTES:

1. PLUG: TYPE EN60320 C14, BLACK
2. CONNECTOR: EN60320 C19 LOCKING, BLACK
3. CORDAGE: SJT3X14/H05VVF3G1.5MM², BLACK
COLOR CODING OF CONDUCTORS: BLUE, BROWN, GREEN/YELLOW
APPROVALS: ENEC, UL, cUL, SAA
RATING: 15A/250V (U.S.), 10A/250V (EUROPE)
4. OPTIONAL LABELS MAY INCLUDE UL, CURRENT AND/OR WARNING.
5. CABLE ASSEMBLIES SHALL BE INDIVIDUALLY PACKAGED.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5] FRACTIONS ± 1/32 .XX = ±.02 [.5] ANGLES ± 1° .XXX = ±.005 [.13]	APPROVALS DRAWN BY VTHANGARAJ CHECKED BY DGUST APPROVED BY GUTTADAURO	DATE 08/29/22 08/29/22 08/29/22	 50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936		
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	CATEGORY POWER PRODUCTS		PRODUCT DESCRIPTION IEC LOCK C19 TO C14, 15A, 250V	
THIRD-ANGLE PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321	ITEM NO. C19LC14-15	REV. A
SCALE: NONE		CAD FILE: C19LC14-15.SLDDRW		SHEET 1 OF 1	