


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	07/20/2022	GUTTADAURO



TABULATION BLOCK	
ITEM NO.	LENGTH $\pm .6$ [15]
C13LPDN515P-15-3F	36.0 [914]
C13LPDN515P-15-6F	72.0 [1829]

NOTES:

1. PLUG: NEMA 5-15P, BLACK
2. CONNECTOR: EN60320 C13 LOCK PLUS, DOWN-ANGLED, BLACK
3. CORDAGE: SJT3X14AWG, BLACK  
COLOR CODING OF CONDUCTORS: BLACK, WHITE, GREEN  
APPROVALS: UL/CSA  
RATING: 15A/125V
4. OPTIONAL LABELS MAY INCLUDE UL, CURRENT AND/OR WARNING.
5. CABLE ASSEMBLIES SHALL BE INDIVIDUALLY PACKAGED.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		 an INFINITE® brand		50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936	
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0		DRAWN BY AKRESOWSK		07/20/2022					
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5]         FRACTIONS .XX = ± .02 [.5]       ± 1/32 .XXX = ± .005 [.13]   ANGLES ± 1°		CHECKED BY DGUST		07/20/2022					
		APPROVED BY GUTTADAURO		07/20/2022		CATEGORY		POWER PRODUCTS	
		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION IEC LOCK C13+ DOWN ANGLED TO NEMA 5-15P, 15A, 125V					
THIRD-ANGLE PROJECTION 		COLOR VARIATIONS MAY OCCUR		SIZE <b>A</b>	CAGE CODE <b>43321</b>	ITEM NO. C13LPDN515P-15		REV. <b>A</b>	
				SCALE: NONE		CAD FILE: C13LPDN515P-15.SLDDRW		SHEET 1 OF 1	