

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	05/11/2023	SREITER	GUTTADAURO

D

D

C


C

B


B

A

A



C14 PLUG



LENGTH

SJT 17AWG/H05VVF3G1.0mm², BLACK
3-COND CORDAGEC13 LOCK PLUS
CONNECTOR

NOTES:

1. PLUG: TYPE C14, BLACK
2. CONNECTOR: C13 LOCK PLUS, BLACK
3. CORDAGE: SJT3X17/H05VVF3G1.0mm², BLACK
4. FOR REFERENCE ONLY:
 - A. COLOR CODING OF CONDUCTORS: BLUE, BROWN, GREEN/YELLOW
 - B. APPROVALS: ENEC, UL, cUL, SAA
 - C. RATING: 10A/250V
5. OPTIONAL LABELS MAY INCLUDE UL, CURRENT AND/OR WARNING.
6. CABLE ASSEMBLIES SHALL BE INDIVIDUALLY PACKAGED.

TABULATION BLOCK	
ITEM NO.	LENGTH ±.6 [15]
C13LPC14-10-3F	36.0 [914]
C13LPC14-10-6F	72.0 [1829]
C13LPC14-10-10F	120.0 [3048]

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		L-com™ an INFINIT® brand		50 High Street, West Mill, North Andover, MA 01845 USA Phone: 1.800.341.5266 1.978.682.6936	
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0		DRAWN BY SREITER		5/11/2023		CATEGORY POWER PRODUCTS		PRODUCT DESCRIPTION IEC LOCK C13+ TO C14, 10A, 250V	
ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5] FRACTIONS ± 1/32 .XX = ±.02 [.5] ANGLES ± 1° .XXX = ±.005 [.13]		CHECKED BY DGUST		05/11/2023					
		APPROVED BY GUTTADAURO		05/11/2023					
THIRD-ANGLE PROJECTION 		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		COLOR VARIATIONS MAY OCCUR		SIZE A		CAGE CODE 43321	
						ITEM NO. C13LPC14-10		REV. A	
						SCALE: NONE		CAD FILE: C13LPC14-10-10F.SLDDRW	
								SHEET 1 OF 1	