



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	05/12/2023	SREITER	GUTTADAURO



"HOSPITAL GRADE" DESIGNATION



NEMA 5-15P  
PLUG

3.26  
[82.8]

LENGTH

SJT 14AWG, BLACK  
3-COND CORDAGE

3.26  
[82.8]

C13 LOCKING  
CONNECTOR

#### NOTES:

1. PLUG: NEMA HG 5-15P, BLACK
2. CONNECTOR: C13 LOCK PLUS, BLACK
3. CORDAGE: SJT3X14AWG, BLACK
4. FOR REFERENCE ONLY:
  - A. COLOR CODING OF CONDUCTORS: BLACK, WHITE, GREEN
  - B. APPROVALS: UL/CSA
  - C. RATING: 15A/125V
5. OPTIONAL LABELS MAY INCLUDE UL, CURRENT AND/OR WARNING.
6. CABLE ASSEMBLIES SHALL BE INDIVIDUALLY PACKAGED.

TABULATION BLOCK	
ITEM NO.	LENGTH ±.6 [15]
C13LPHGN515-15-3F	36.0 [914]
C13LPHGN515-15-6F	72.0 [1829]
C13LPHGN515-15-10F	120.0 [3048]

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]  OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0  ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5]      FRACTIONS ± 1/32 .XX = ±.02 [.5]      ANGLES ± 1° .XXX = ±.005 [.13]  THIRD-ANGLE PROJECTION 	APPROVALS	DATE	 an INFINITI® brand  50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936
	DRAWN BY SREITER	05/12/2023	
	CHECKED BY DGUST	05/12/2023	
	APPROVED BY GUTTADAURO	05/12/2023	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	CATEGORY  POWER PRODUCTS		PRODUCT DESCRIPTION IEC LOCK C13+ TO HG NEMA 5-15P, 15A, 125V
COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321	ITEM NO. C13LPHGN515-15
SCALE: NONE		CAD FILE: C13LPHGN515-15-10F.SLDDRW	REV. A
		SHEET 1 OF 1	