

Product data sheet

Specifications

SQUARE D

Green Premium™



Contactor, Type L, multipole lighting, electrically held, 30A, 8 pole, 600 V, 110/120 VAC 50/60 Hz coil, NEMA 4/4X

8903LW80V02

Product availability : Non-Stock - Not normally stocked in distribution facility

Main

Product or Component Type	Electrically Held Lighting Contactor
Range of Product	8903L
Control Circuit	Separate control circuit

Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Inrush power in VA	180 VA 60 Hz 170 VA 50 Hz
Hold-in power consumption in VA	35 VA 60 Hz 35 VA 50 Hz
Current Rating	20 A tungsten 30 A fluorescent
Number of Poles	8P 8 NO
Control Unit	No control units
Pilot Light	No indicator
Electrical Connection	Screw-clamp terminals
Height	16.18 in (411 mm)
Depth	7.87 in (200 mm)
Width	8.11 in (206 mm)

Environment

Enclosure Type	NEMA 4/4X brushed stainless steel surface
Product Certifications	UL Listed CSA

Ordering and shipping details

Category	21321 - 8903 L (NOT LX)
Discount Schedule	CP1
GTIN	785901821199
Returnability	No

Country of origin	MX
-------------------	----

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	16.18 in (41.1 cm)
Package 1 Width	8.11 in (20.6 cm)
Package 1 Length	7.87 in (20.0 cm)
Package 1 Weight	21.78 lb(US) (9.88 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)