




P	LTR	DESCRIPTION	DATE	DWN	APVD
	4	UPDATE TOLERANCE OF 23.2 AND 26.2	28AUG2021	JZ	WKH
	5	ADD A1~D1, PCB 3.0+/-0.2	13SEP2021	JZ	WKH
	6	UPDATE PCB LAYOUT	09NOV2021	PZ	WKH
	A	GTP PER ECN-24-262413	07MAY2024	ED	WH





- NOTES:
- MATERIAL:
HOUSING - THERMOPLASTIC, BLACK
CONTACTS- COPPER ALLOY
 - FINISH:
MATING AREA - GOLD OVERALL NICKEL
 - STRADDLE MOUNT PCB THICKNESS 3MM
 - PART NUMBER AND 6 DIGIT DATA CODE(YYWWDS), ANNOTATION HEIGHT TO BE BETWEEN 1.27 AND 2.36, LOCATE APPROX AS SHOWN, MARKING ON EITHER SIDE PERMITTED.


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JULIA ZHU 27AUG2021	TE Connectivity		
		CHK WENKE HE 27AUG2021			
DIMENSIONS: mm		APVD -	NAME MULTI-CHANNEL RF CONNECTOR 64 CHANNELS, STRADDLE TYPE -		
		PRODUCT SPEC -			
		APPLICATION SPEC -	SIZE A3		
		WEIGHT -			
MATERIAL SEE NOTE -		FINISH SEE NOTE -	CAGE CODE 00779		
			DRAWING NO C-2081996		
			RESTRICTED TO -		
			SCALE 2:1		
			SHEET 1 OF 2		
			REV A		

RECOMMENDED PCB LAYOUT

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JULIA ZHU 27JUL2021	 TE Connectivity		
DIMENSIONS: mm		CHK WENKE HE 27JUL2021			
		APVD -	NAME MULTI-CHANNEL RF CONNECTOR 64 CHANNELS, STRADDLE TYPE		
		PRODUCT SPEC -	-		
MATERIAL SEE NOTE		APPLICATION SPEC -	SIZE A3		
		WEIGHT -	CAGE CODE 00779		
FINISH SEE NOTE		CUSTOMER DRAWING	DRAWING NO C-2081996		
-		SCALE 2:1	SHEET 2 OF 2		REV A