




12		11		10		9		8		7		6		5		4		3		2		1	
0.50mm CENTER FLAT FLEX CABLE (FFC) (105°C, Au PLATED)																							
"L" DIM. →	51 ± 2 MM		76 ± 3 MM		102 ± 3 MM		127 ± 4 MM		152 ± 4 MM		178 ± 4 MM		203 ± 4 MM		229 ± 5 MM		254 ± 5 MM		305 ± 5 MM				
REF DIM →	(2 INCHES)		(3 INCHES)		(4 INCHES)		(5 INCHES)		(6 INCHES)		(7 INCHES)		(8 INCHES)		(9 INCHES)		(10 INCHES)		(12 INCHES)				
CABLE TYPE →	A	D	A	D	A	D	A	D	A	D	A	D	A	D	A	D	A	D	A	D			
CIRCUITS "N" ↓																							
10	173280210	173282210	173280310	173282310	173280410	173282410	173280510	173282510	173280610	173282610	173280710	173282710	173280810	173282810	173280910	173282910	173281010	173283010	173281210	173283210			
15	173280215	173282215	173280315	173282315	173280415	173282415	173280515	173282515	173280615	173282615	173280715	173282715	173280815	173282815	173280915	173282915	173281015	173283015	173281215	173283215			
20	173280220	173282220	173280320	173282320	173280420	173282420	173280520	173282520	173280620	173282620	173280720	173282720	173280820	173282820	173280920	173282920	173281020	173283020	173281220	173283220			
28	173280228	173282228	173280328	173282328	173280428	173282428	173280528	173282528	173280628	173282628	173280728	173282728	173280828	173282828	173280928	173282928	173281028	173283028	173281228	173283228			
30	173280230	173282230	173280330	173282330	173280430	173282430	173280530	173282530	173280630	173282630	173280730	173282730	173280830	173282830	173280930	173282930	173281030	173283030	173281230	173283230			
40	173280240	173282240	173280340	173282340	173280440	173282440	173280540	173282540	173280640	173282640	173280740	173282740	173280840	173282840	173280940	173282940	173281040	173283040	173281240	173283240			
45	173280245	173282245	173280345	173282345	173280445	173282445	173280545	173282545	173280645	173282645	173280745	173282745	173280845	173282845	173280945	173282945	173281045	173283045	173281245	173283245			
50	173280250	173282250	173280350	173282350	173280450	173282450	173280550	173282550	173280650	173282650	173280750	173282750	173280850	173282850	173280950	173282950	173281050	173283050	173281250	173283250			
55	173280255	173282255	173280355	173282355	173280455	173282455	173280555	173282555	173280655	173282655	173280755	173282755	173280855	173282855	173280955	173282955	173281055	173283055	173281255	173283255			
60	173280260	173282260	173280360	173282360	173280460	173282460	173280560	173282560	173280660	173282660	173280760	173282760	173280860	173282860	173280960	173282960	173281060	173283060	173281260	173283260			
64	173280264	173282264	173280364	173282364	173280464	173282464	173280564	173282564	173280664	173282664	173280764	173282764	173280864	173282864	173280964	173282964	173281064	173283064	173281264	173283264			
68	173280268	173282268	173280368	173282368	173280468	173282468	173280568	173282568	173280668	173282668	173280768	173282768	173280868	173282868	173280968	173282968	173281068	173283068	173281268	173283268			
74	173280274	173282274	173280374	173282374	173280474	173282474	173280574	173282574	173280674	173282674	173280774	173282774	173280874	173282874	173280974	173282974	173281074	173283074	173281274	173283274			
80	173280280	173282280	173280380	173282380	173280480	173282480	173280580	173282580	173280680	173282680	173280780	173282780	173280880	173282880	173280980	173282980	173281080	173283080	173281280	173283280			



END TAIL DETAIL
SCALE 8:1

- NOTES:
- NO PRINTING ON JUMPER CABLE UNLESS OTHERWISE SPECIFIED. IF PRINTING IS REQUIRED, THEN IT WOULD BE CONSIDERED A SPECIAL JUMPER CABLE.
 - INTERMATEABLE WITH HIROSE FH28 0.50 mm SERIES



CROSS-SECTION

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
FUNCTIONAL SYMBOLS FA =0 FE =0 FP =0 DIVISIONAL SYMBOLS	DIMENSION UNITS		SCALE		CURRENT REV DESC: CUSTOMER RESTRICTION REMOVAL				molex 0.50MM CENTER FLAT FLEX CABLE (FFC) (105°C, AU PLATED) SALES DRAWING						
	mm		2:1												
	GENERAL TOLERANCES (UNLESS SPECIFIED)														
	mm		INCH												
	4 PLACES		±0	±0					STATUS:Production DRWN: DIEGO GOMEZ 2024-05-01 CHK'D: MATTHEW IMIG 2024-05-01 APPR: DAVID FALLA 2024-05-01						
	3 PLACES		±0	±0											
	2 PLACES		±0	±0											
	1 PLACE		±0	±0											
	0 PLACES		±0	±0											
	ANGULAR TOL ± 0.5 °								PRODUCT DESIGN DRAWING						
DOCUMENT NUMBER								DOC TYPE		DOC PART		REVISION			
173280001								PSD		000		D			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
						C-SIZE		17328		SEE CHART		GENERAL MARKET		1 OF 1	

molex

0.50MM CENTER FLAT FLEX CABLE (FFC)
(105°C, AU PLATED) SALES DRAWING

PRODUCT DESIGN DRAWING

DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
173280001	PSD	000	D