


NUMBER C-179518

179518-1 : 本 ☒

179518-1 : AS SHOWN



注;

- 1 材料 錫めつき済燐青銅 (板厚0.2)
- 2 適用製品規格; 108-5408
- 3 取付適用規格; 114-5179
- 4 連鎖状端子型番; 179227-1 (折取り部なし)

NOTES;

- 1 MATERIAL PRE-TIN PHOS.BRO (THK 0.2)
- 2 PRODUCT SPEC. ; 108-5408
- 3 APPLICATION SPEC. ; 114-5179
- 4 STRIP TERMINAL ; 179227-1 (W/O NOTCH)

DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT

Copyright © 19__
AMP (Japan) .LTD.
ALL RIGHTS RESERVED.

AMP
AMP (JAPAN), LTD.
Tokyo, Japan

GENERAL TOLERANCE 0\leq 10 ; ± 0.2 10\leq 30 ; ± 0.25 30\leq 100 ; ± 0.3 ANGLES ; $\pm 3^\circ$	WIRE RANGE 0.12 -0.37 mm ² (AWG 26-22)	INSULATION DIA. 0.93-1.5 mm ϕ
MATERIAL SEE NOTE 1	FINISH SEE NOTE 1	

DR. J. Furuya 3/15/84	DE. J. Furuya 3/15/84	SCALE	SIZE	LOC	NUMBER	REV.	SHEET
CHK. S. Kubouchi 3/15/84	APP. S. Kubouchi 3/15/84	—#—	A	J	C-179518	0	1 OF 1
NAME CRIMP TYPE II REC. CONTACT (L/P) 圧着タイプIIリセコンタクト (バラ状) (AMP CTコネクタ 2mmピッチ) (AMP CT CONN. 2mm PITCH)							