




0.50MM LVDS FLAT FLEXIBLE CABLE (FFC)							
"L" DIM.	51 ± 2 MM	102 ± 4 MM	152 ± 4 MM	203 ± 5 MM	254 ± 5 MM	305 ± 5 MM	610 ± 5 MM
REF DIM →	(2 INCHES)	(4 INCHES)	(6 INCHES)	(8 INCHES)	(10 INCHES)	(12 INCHES)	(24 INCHES)
CABLE TYPE →	A						
CKTS "N" ↓							
30	159220230	159220430	159220630	159220830	159221030	159221230	159222430
40	159220240	159220440	159220640	159220840	159221040	159221240	159222440
50	159220250	159220450	159220650	159220850	159221050	159221250	159222450



TAIL CROSS-SECTION

NOTES:

1. NO PRINTING ON JUMPER CABLE UNLESS OTHERWISE SPECIFIED. IF PRINTING IS REQUIRED, THEN IT WOULD BE CONSIDERED A SPECIAL JUMPER CABLE.
2. CABLES MATE WITH MOLEX FFC/FPC CONNECTOR SERIES 501786 & 501864

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
DIMENSION UNITS		SCALE		CURRENT REV DESC: PRODUCTION RELEASE				molex 0.50MM PITCH 90 OHM LVDS FFC CABLE SALES DRAWING					
MM		NA											
GENERAL TOLERANCES (UNLESS SPECIFIED)													
	mm	INCH		STATUS:Production				PRODUCT SALES DRAWING					
4 PLACES	± ----	± ----											
3 PLACES	± ----	± 0.01											
2 PLACES	± ----	± 0.03											
1 PLACE	± ----	± ----											
0 PLACES	± ----	± ----		DRWN: DIEGO GOMEZ		2024-05-07		DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION	
ANGULAR TOL ± ---- °				CHK'D: MATTHEW IMIG		2024-05-08		159220001		PSD	000	A	
APPR: DAVID FALLA				2024-05-08									
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER	SHEET NUMBER
						C-SIZE		15922		159220001		GENERAL MARKET	1 OF 1