




0.50MM LVDS FLAT FLEXIBLE CABLE (FFC)							
"L" DIM.	51 ± 2 MM	102 ± 4 MM	152 ± 4 MM	203 ± 5 MM	254 ± 5 MM	305 ± 5 MM	610 ± 5 MM
REF DIM →	(2 INCHES)	(4 INCHES)	(6 INCHES)	(8 INCHES)	(10 INCHES)	(12 INCHES)	(24 INCHES)
CABLE TYPE →	A						
CKTS "N" ↓							
30	159220230	159220430	159220630	159220830	159221030	159221230	159222430
40	159220240	159220440	159220640	159220840	159221040	159221240	159222440
50	159220250	159220450	159220650	159220850	159221050	159221250	159222450



TAIL CROSS-SECTION

NOTES:

- NO PRINTING ON JUMPER CABLE UNLESS OTHERWISE SPECIFIED. IF PRINTING IS REQUIRED, THEN IT WOULD BE CONSIDERED A SPECIAL JUMPER CABLE.
- CABLES MATE WITH MOLEX FFC/FPC CONNECTOR SERIES 501786 & 501864

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
DIMENSION UNITS		SCALE		CURRENT REV DESC: PRODUCTION RELEASE				molex 0.50MM PITCH 90 OHM LVDS FFC CABLE SALES DRAWING				
MM		NA										
GENERAL TOLERANCES (UNLESS SPECIFIED)				PRODUCT SALES DRAWING								
		mm	INCH									
4 PLACES		± ----	± ----	STATUS:Production DRWN: DIEGO GOMEZ2024-05-07 CHK'D: MATTHEW IMIG2024-05-08 APPR: DAVID FALLA2024-05-08				DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION
3 PLACES		± ----	± 0.01					159220001		PSD	000	A
2 PLACES		± ----	± 0.03									
1 PLACE		± ----	± ----									
0 PLACES		± ----	± ----					MATERIAL NUMBER		CUSTOMER		SHEET NUMBER
ANGULAR TOL ± ---- °				THIRD ANGLE PROJECTION	DRAWING	SERIES	159220001	GENERAL MARKET		1 OF 1		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS					C-SIZE	15922						