

1				2				3				4							
△數 COUNT		訂正事項 DESCRIPTION OF REVISIONS		擔當 B Y		檢圖 CHKD		年月日 DATE		△數 COUNT		訂正事項 DESCRIPTION OF REVISIONS		擔當 B Y		檢圖 CHKD		年月日 DATE	
△								. .		△								. .	
△								. .		△								. .	
△								. .		△								. .	

±45° MAX

100 ±4

(0.64 Dia)

①

② WHITE

①

Dimensions of Connector

2.1 ±0.2

(3.3)

0.9 ±0.2

12 MAX

[MATED CONDITION]

K.FL2-LP-040

K.FL2-R-SMT-1

◆ Allowable loads on the cable after the connectors are mated.

The figures below show the maximum allowable loads on the cable. Do not apply loads exceeding these values th the cable.

PLUG

RECEPTACLE

CABLE

X

2N MAX

X

1	K.FL2-LP-040	CL6345-****	2	0.64 Dia. coaxial cable(WHITE)					
NO.	PART NO.	CORD NO.	NO.	PART NO.					
CODE NO. (OLD)		DRAWN			DESIGNED	CHECKED	APPROVED	RELEASED	
		W.Y.AHN 19.01.18			W.Y.AHN 19.01.18	H.S.KIM 19.01.18	H.S.KIM 19.01.18	ENG 19.01.25 DEPT	
		DRAWING NO. EDC4-632765-80			PART NO. KFL22LP-044H1TS-A100 (800)				
SCALE FREE		HRS HIROSE KOREA CO.,LTD.			CODE NO CL6345-0147-4-800				
UNITS mm									1/1