







CONTACT SIZE	MIN. INSUL O.D.	MAX. INSUL O.D.	TYPICAL WIRE RANGE	CURRENT RATING
20	1.02 mm (.040 in)	2.41 mm (.095 in)	16-22 AWG (1.5-0.35mm ²)	7.5 AMPS



RECOMMENDED PANEL THICKNESS:1.6 TO 4.7MM



REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
A1	--	RELEASE NEW DRAWING	17/JAN/24	LYNCH	TOMMY

AHPD04-24-33SN-SRA

QUANTITY

PART NUMBER

REF:HPD24-24-33SN

DESCRIPTION

ITEM NO.

MATERIALS LIST

UNLESS OTHERWISE SPECIFIED

1) All dimensions are in metric(mm).

2) Tolerances are as follows:

1 PL DEC ±0.50 Fractions ±1/64

2 PL DEC ±0.15 Angles ±1°

3 PL DEC ±0.08

3) Note reference = 

MATERIAL SPECIFICATIONS:

WEIGHT: 64.87g

PROCESS SPECIFICATIONS:

NEXT ASSY:

SIGNATURES

DATE

DRAWN: LYNCH, PAN

17/JAN/24

CHECKED: SULLEN, ZHANG

18/JAN/24

ENGINEER:

APPROVAL: TOMMY, XIE

19/JAN/24

CUSTOMER:

THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.

Amphenol

Sine Systems - www.amphenol-sine.com

44724 Morley Drive

Clinton Township, MI 48036

RECEPT, SIZE 24,33 SOCKET,

NORMAL SEAL, SRA,DURAMATE AHPD SERIES

SIZE

B

TYPE

C-

DWG NO:

AHPD04-24-33SN-SRA

REVISION

A1

SCALE:

NONE

DURAMATE

SHEET 1 OF 1

7. RECEPTACLE IS SUPPLIED WITH DUST CAP.