



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B1	REVISED AS PER ECN-22-135706	21JAN2022	RB	MT



DIMENSIONS IN EXPANDED CONDITION


NOTES:

1.HEATSHRINK MATERIAL: SEMI-RIGID THERMOPLASTIC MATERIAL,ELECTRICALLY INSULATING, WEATHER, CORROSION AND IMPACT RESISTANT. STABILIZED AGAINST UV IRRADIATION. COLOUR=BLACK

2.DIMENSIONS IN mm.
a = AS SUPPLIED.
b = AFTER FREE RECOVERY.



3.HOTMELT ADHESIVE COATING PROVIDES WATER TIGHT AND ENVIRONMENTAL SEAL. COATING LOCATION AND DIMENSIONS AS DEFINED IN THE DRAWING.

TCPN NO	DESCRIPTION	Ha MIN	Pa MIN	Ra		S	
				MIN	MAX	MIN	MAX
631054-000	ENC-11/ADH-0	12	46	39	44	FULL	-
047688-000	ENC-22/ADH-0	18	57.7	45	55	32.5	37.5
223762-000	ENC-33/ADH-0	35	102.7	81	99	45	55
063206-000	ENC-44/ADH-0	55	155.2	120.6	147.4	75	85
498716-000	ENC-48/ADH-0	75	195	160	180	119	131
061320-000	ENC-55/ADH-0	100	184.7	129.6	158.4	95	105

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RANJITHA B 24AUG2021	 TE Connectivity			
		CHK PRZYBYLSKA, NINA 08/24/2021				
DIMENSIONS: mm		APVD MARK, TAYLOR 08/24/2021	NAME END CAP (ENC)			
		PRODUCT SPEC	-			
		APPLICATION SPEC	-			
MATERIAL -		WEIGHT -	SIZE A3	CAGE CODE 06090	DRAWING NO C-ENC-XX/ADH-0	RESTRICTED TO -
CUSTOMER DRAWING			SCALE DNS	SHEET 1 OF 2	REV B1	


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

SECTION A—A



DIMENSIONS IN RECOVERED CONDITION

TCPN NO	DESCRIPTION	Hb MAX	Pb		Rb		Wb MIN	
			MIN	MAX	MIN	MAX	MIN	MAX
631054-000	ENC-11/ADH-0	04	44	48	40	45	2.30	3.11
047688-000	ENC-22/ADH-0	7.5	49.5	63.25	45	57.5	2.24	3.36
223762-000	ENC-33/ADH-0	15	81	103.5	72	92	2.56	3.84
063206-000	ENC-44/ADH-0	25	128.7	164.45	117	149.5	3.168	4.75
498716-000	ENC-48/ADH-0	32	165	185	150	175	2.64	3.96
061320-000	ENC-55/ADH-0	45	145.8	186.3	126	161	3.04	4.56



THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 24AUG2021
RANJITHA B
CHK 08/24/2021
PRZYBYLSKA, NINA
APVD 08/24/2021
MARK, TAYLOR
PRODUCT SPEC
—
APPLICATION SPEC
—
WEIGHT —



TE Connectivity

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± — FINISH —
MATERIAL —	FINISH —

END CAP (ENC) —					RESTRICTED TO
SIZE	CAGE CODE	DRAWING NO			
A3	06090	C-ENC-XX/ADH-0			—
CUSTOMER DRAWING			SCALE	SHEET	REV
			DNS	2 OF 2	B1