




Part No.	Cable color
~062*1D~	GRAY
~062*2D~	BLACK

NOTE 1 We indicate the length of the harness on the last of product name, 'L' part.


2 Tolerance for [L]

Length L [mm]	Tolerance [mm]
$35 \leq L \leq 200$	± 4
$200 < L \leq 500$	± 8
$500 < L \leq 1000$	± 12
$1000 < L$	$\pm 1.5\%$

3 Connector rotation angle is within ± 45 degree from the above image.
For long length in the case of $L > 500$, the angle is optional.

4. Specifications are subject to change without notice.

【 DIMENSIONS OF CONNECTOR 】



1	U.FL-LP-062HF(06)	CL331-0561-0-06	2	0.95 Dia. coaxial cable
NO.	PART NO.	CODE NO.	NO.	PART NO.

HALOGEN FREE

UNITS mm	SCALE FREE	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
			APPROVED : NK. NINOMIYA 18.06.22	DRAWING NO.		
			CHECKED : MT. KANEKO 18.06.22	PART NO.		
			DESIGNED : MS. MATSUMOTO 18.06.22	CODE NO.		
			DRAWN : MS. MATSUMOTO 18.06.22			

HRS HIROSE
ELECTRIC
CO., LTD.

APPROVED : NK. NINOMIYA 18.06.22
CHECKED : MT. KANEKO 18.06.22
DESIGNED : MS. MATSUMOTO 18.06.22
DRAWN : MS. MATSUMOTO 18.06.22

DRAWING NO. UFL-2LPHF6-062**D-AC-L 1
PART NO.
CODE NO.