




Connector Location A

Connector Location B



Loading Plan

1	brown
3	blue
4	black



100	+1%
50 to 99	+0.5
20 to 49	+0.35
10 to 19	+0.25
5 to 9.9	+0.20
2 to 4.9	+0.15
1 to 1.9	+0.10
0.5 to 0.9	+0.07
0.2 to 0.4	+0.04
0.1	+0.03
a [m]	Tolerance

length in "1m" step	100	XXX=000
	99	XXX=990
	.	.
	.	.
	12	XXX=120
length in "0.1m" step	11	XXX=110
	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
Step	0.5	XXX=005
	0.4	XXX=004
	0.3	XXX=003
	0.2	XXX=002
	a [m]	XXX

- Protection level: IP67
- Temperature range: -25°C ... +80°C

PUR black, 3x0.25mm ²	21340400312XXX
Type of cable	Part no.

All Dimensions in mm		Tech. Character.		Free size tol.		According to production drawing	
	All rights reserved	Created by BANCUD Banciu	Inspected by COSTEA Costea	Standardisation MUNTEANV Muntean	Date 2022-07-22	State Final Release	
	Department HCS - RO	Title M5 A-cod 3-pol st/- f/- PUR				Doc-Key / ECM-Nr. 101016903/UGD/000/B 500000221275	
HARTING Customised Solutions D-32339 Espelkamp		Type TB	Number 21340400312XXX			Rev. B	Page 1/1