



Connector Location A

Connector Location B




X
male

Y
female




Loading Plan

1	brown	1
2	white	2
3	blue	3
4	black	4
FE	grey	FE



- Protection level: IP65/67
- Temperature range: -25°C ... +80°C



3.1 to 100	±1.5%
1.1 to 3.0	+0.1
0.6 to 1.0	+0.05
0.2 to 0.5	+0.03
a [m]	Tolerance

length in "1m" step	100	XXX=000
	99	XXX=990
	.	.
	12	XXX=120
	11	XXX=110
length in "0.1m" step	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	0.5	XXX=005
Step	0.4	XXX=004
	0.3	XXX=003
	0.2	XXX=002
Step	a [m]	XXX

PUR black 5x1.5mm ²	21343031543XXX
Type of cable	Part no.



All rights reserved
Department HCS - RO
HARTING Customised Solutions
D-32339 Espelkamp

Created by
407576
Stoica

Inspected by
COSTEA
Costea

Standardisation
BANIUD
Banciu

Date
2023-11-08

State
Final Release

Doc-Key / ECM-Nr.
100955603/UGD/001/B
500000256959

Rev. B

Page 1/1

Technical Character.

Free size tol.

According to production drawing

Title
M12 L-cod 4+FE st/st m/f PUR

Type TB

Number 21343031543XXX