












Tauchlötanschluss 0,3 x 0,7mm
solder terminal 0,3 x 0,7 mm

Anforderungsstufe 2 = 400 Steckzyklen
performance class 2 = 400 mating cycles

Fehlende Maße und Angaben nach IEC 60 603-2 / DIN EN 60 603-2
Missing information and dimensions per IEC 60 603-2 / DIN EN 60 603-2

Dimension no.				Tolerances Din. for Information ISO 8015		 All Dimensions in mm		Scale 2:1		Tool-no.	
Customer drawing: THIS DRAWING IS A CONTROLLED DOCUMENT.				Subject to modification without prior notice. Drawing will not be updated		ERNI-DIN 41612 / IEC-60603-2 Female Connector Q/2 32 Solder Type 7					
						C-294722-E					
				a		0085-21		26.05.2021		Grünenwald	
Index		Modification Nr.		Date		Name					