


TABLE 1	
MODEL NUMBER	LENGTH
415-0503-006	6.00±.15
415-0503-012	12.00±.25
415-0503-018	18.00±.25
415-0503-024	24.00±.25
415-0503-036	36.00±.50

REV	ECO	DATE
1	INITIAL RELEASE	04/24/2023
2	EC-2408008	08/15/2024



NOTES: UNLESS OTHERWISE SPECIFIED.

1. CABLE ASSEMBLY DIELECTRIC WITHSTANDING VOLTAGE: 500 VRMS FOR A PERIOD OF ONE MINUTE.
2. CABLE ASSEMBLIES TO BE 100% TESTED FOR VOLTAGE AND CONTINUITY.
3. ASSEMBLIES TO BE PACKAGED 1 PER BAG.
4. VSWR: 1.50 MAX DC-18GHz

PART LIST		
ITEM	QTY	DESCRIPTION
1	2	SMP FEMALE
2	AR	CABLE
3	2 X1.00±.10	HEAT SHRINK TUBING

This PROPRIETARY Document is property of Cinch Connectivity Solutions. It is confidential in nature, non-transferable, and issued with the clear understanding that it is not traced or copied without permission and is returnable upon demand. INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2018.	Model No:	415-0503-001/999		JOHNSON	
	RoHS ☒ (EU)/2015/863 COMPLIANT	Cage Code	34078	Title: CABLE ASSY, STR SMP FEMALE TO STR SMP FEMALE, .086" FLEXIBLE Drawing No. 415-0503-001/999 Size A DO NOT SCALE DRAWING	
	UNLESS OTHERWISE SPECIFIED UNITS: INCH	3RD ANGLE PROJECTION			
	.XX ± .01 .XXX ± .003 .XXXX ± .0010 ANGLE ± 2°	Drawn by: JIMMY CHEN	Date: 04/24/2023	Workmanship Std: NONE	REV. 2 1 OF 1