


TABLE 1	
MODEL NUMBER	LENGTH
415-0509-006	6.00±.15
415-0509-012	12.00±.25
415-0509-018	18.00±.25
415-0509-024	24.00±.25
415-0509-036	36.00±.50

REV	ECO	DATE
1	INITIAL RELEASE	04/24/2023
2	EC-2408008	08/15/2024



PART LIST		
ITEM	QTY	DESCRIPTION
1	2	SMP FEMALE
2	2 X .40±.10	HEAT SHRINK TUBING
3	AR	CABLE

NOTES: UNLESS OTHERWISE SPECIFIED.

1. CABLE ASSEMBLY DIELECTRIC WITHSTANDING VOLTAGE: 500 VRMS FOR A PERIOD OF ONE MINUTE.
2. CABLE ASSEMBLIES TO BE 100% TESTED FOR VOLTAGE AND CONTINUITY.
3. ASSEMBLIES TO BE PACKAGED 1 PER BAG.
4. VSWR: 1.50 MAX DC-18GHz

This PROPRIETARY Document is property of Cinch Connectivity Solutions. It is confidential in nature, non-transferable, and issued with the clear understanding that it is not traced or copied without permission and is returnable upon demand. INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2018.	Model No:	415-0509-001/999		JOHNSON	
	RoHS ☒ (EU)/2015/863 COMPLIANT	Cage Code	34078	Title: CABLE ASSY, STR SMP FEMALE TO STR SMP FEMALE, .047" FLEXIBLE	
	UNLESS OTHERWISE SPECIFIED UNITS: INCH	3RD ANGLE PROJECTION		Drawing No.	REV.
	.XX ± .01 .XXX ± .003 .XXXX ± .0010 ANGLE ± 2°	Drawn by: JIMMY CHEN Date: 04/24/2023	Size: A	415-0509-001/999 DO NOT SCALE DRAWING	2 1 OF 1