



REVISIONS

REV	DESCRIPTION	DATE	DWN	APVD
1	PRELIMINARY RELEASE	29 OCT 2024	MA	




2 PORTS

4 PORTS



MECHANICAL & ENVIRONMENTAL SPECIFICATIONS

NUMBER OF PORTS	2	4
TE PART NUMBER	L000962-01	L000962-02
ALIAS	PSD24718-75RSMM	PSQ24718-75RSMM
WEIGHT	0.43 kg (Antenna Itself) 0.58 kg (In Carton)	0.54 kg (Antenna Itself) 0.69 kg (In Carton)
DIMENSIONS	200mm (W) x 200 mm (L) x 46.5 mm(H) (Antenna itself) 250mm (W) x 220 mm (L) x 58 mm (H) (Unit carton)	
HOUSING	MATERIAL: ASA, Luran S 788T, UV and Color: White	
CABLE LENGTH(CM) / CONECTOR TYPE / QUANTITY PER ASSEMBLY	75±1.5 PLENUM RATED RG58LL / RP-SMA-MALE / 2	75±1.5 PLENUM RATED RG58LL / RP-SMA-MALE / 4
TEMPERATURE RANGE (°C)	-50 TO 65	
IP RATING	IP67	



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ARFAN	PRELIMINARY TE Connectivity			
DIMENSIONS: mm		CHK				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD				
0 PLC ± 0.5 1 PLC ± 0.25 2 PLC ± 0.13 3 PLC ± 4 PLC ± ANGLES ± 30'		PRODUCT SPEC				
MATERIAL		FINISH	NAME PANEL, TRI-BAND, 75CM, RP-SMAM 2.4-7.125 GHz, 8dBi			
WEIGHT		REFER TABLE	SIZE A3	CAGE CODE 00779	DRAWING NO C=L000962	RESTRICTED TO —
CUSTOMER DRAWING				SCALE 1:4	SHEET 1 OF 1	REV 1