





PRODUCT No.
10174587-XX0000LF



PIN	DIMA	DIMB
03	5.00	9.55
05	10.00	14.55

Notes
1.Material:
Housing : Thermoplastic (UL94V-0)
Contact : Copper Alloy
2.Finish
Contact Plated : Gold Plating
3.Specification
Current Rating : 5A
Contact Resistance : 30mΩ
Insulation Resistance : 100MΩ
Dielectric Voltage : 500V
Operating Temperature : -40°~105°

10174587-XX0000LF
PIN No.: 03: 3Pin
05: 5Pin



PCB LAYOUT PROPOSAL
TOLERANCE RECOMMENDED ±0.05

spec ref				dr		Hao-Liang Sun		2024/09/18		projection		mm		size		A3		scale		5:1											
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED						eng						Hao-Liang Sun		2024/10/09		ecn no													
								chr						-		-															
				appr		Tim Yao		2024/10/09		product family						rel level: Released															
surface		✓		linear		0.X		±0.35		Amphenol FCI		title		Header VT 2.5mm Pitch						dwg no		10174587						rev		A	
						0.XX		±0.25																							
						0.XXX		±0.15																							
				angular		0°		±2°		amphenol-icc.com		cat. no.				Product - Customer Drw						sheet 1 of 1									