




SYM	ECN	DESCRIPTION	DATE	APPROVED
0A	---	FIRST RELEASE	08/01'24	Dam



LABEL:




WIRE LIST:



NOTES:

- PRODUCT MUST COMPLY TO THE LATEST LEVEL OF SAE/USCAR30.
- ELECTRICAL PERFORMANCE:
CURRENT RATING: 5A
INSULATION RESISTANCE: 5MΩ MIN. (200V DC)
- MECHANICAL PERFORMANCE:
DURABILITY: 10 CYCLES MIN.
TEMPERATURE RANGE: -40°C TO +105°C
- MATERIAL SHOULD BE FULFILLED RoHS REQUIREMENT AND AMPHENOL SPEC# SSN002.

5. ORDER P/N SYSTEM:



HF(无卤)	
Non-HF(有卤)	✓

2	CONNECTOR	MINI HSBRIDGE+ USB C PLUG CABLE CONNECTOR CODE-A	2
1	RAW CABLE	USB3.1 FEP,(30AWG-1P+EAM)×4+(30AWG-1P+AM)×(32AWG-1C)×4+21AWG×1C,0D5.2	A/R
ITEM	NAME	DESCRIPTION	QUANTITY
UNLESS OTHERWISE SPECIFIED TOLERANCES			
U.S.		APPROVAL	DATE
0 +/-		DRAWN Simon	08/01'24
0.00 +/-		CHECKED Johnny	08/01'24
FRACTIONS +/-		CHECKED	
ANGLES +/-			
FOR MATERIALS AND FINISHES SEE NOTES			
REMOVE SHARP EDGES			
DIMENSIONS			
U.S.		INCHES	
(METRIC)		(MM)	
ANGLE OF PROJECTION			
TITLE			
Amphenol			
Amphenol East Asia Limited			
CUSTOMER DRAWING FOR MINI HSBRIDGE+ USB C PLUG TO PLUG CABLE, CODE A-A, L=1000MM			
SIZE	DRAWING NO.	REV.	
A3	USBCC211AA016AS	0A	
SCALE	N/A	SHEET 1 OF 1	