








VIEW C →




VIEW C (PARTLY VIEW)
SCALE 15:1




SECTION A-A
SCALE 15:1



SECTION B-B
SCALE 15:1



DETAIL D
SCALE 4:1



PACKAGE: 20K PCS/REEL
5 REEL/BOX
100K PCS/BOX

NOTES:

1. MATERIAL: COPPER ALLOY, T=0.15mm.
2. DIMENSIONING SHALL BE INTERPRETED PER ASME Y14.5-2009
3. PRODUCT DESCRIPTION CODE: 10175510-X 0 X LF

PLATING OPTION:

- 0 → 1~3um MATTE TIN PLATED OVER ALL
- 1 → 0.05um Min. GOLD ON CONTACT AREA
MATTE TIN ON CRIMPING AREA
- 2 → 0.38um Min. GOLD ON CONTACT AREA
MATTE TIN ON CRIMPING AREA
- 3 → 0.76um Min. GOLD ON CONTACT AREA
MATTE TIN ON CRIMPING AREA

APPLICATION WIRE
1 → AWG#26~30

spec ref				dr	Jeffrey Huang	2025/02/27	projection	mm	size	A3	scale	10:1
tolerance std				eng	Jeffrey Huang	2025/02/27			ecn no			
ISO 406				chr	-	-			rel level			
ISO 1101				appr	Tim Yao	2025/02/27			Released			
TOLERANCES UNLESS OTHERWISE SPECIFIED												
surface		linear	0.X	±0.30	Amphenol FCi	title			dwg no	10175510		rev
ISO 1302			0.XX	±0.15		Receptacle Terminal						
			0.XXX	±0.05		DensiMate Series Connector						
		angular	0°	±2°	cat. no.			Product - Customer Drw			sheet 1 of 1	