

SnapLock hood/
SnapLock Haube

Cable/
Kabel

D-SUB Male 15pos./
D-SUB Stift 15pol.

Mounting material
for SnapLock/
Montagematerial
für SnapLock

**Materials SnapLock hood/
Werkstoffe SnapLock Haube:**

Hood/
Haube: ABS UL 94 V-0, Ni

Blanking plug/
Blindstopfen: ABS UL 94 V-0, Ni

Cable strain relief/
Zugentlastung: Steel, Ni

Clip/
Clip: Stainless Steel/
Edelstahl

Countersunk-head screw/
Linsenkopfschraube: Steel, Ni

Mounting material/
Montagematerial: Steel, Ni

**Materials D-SUB Male 15pos./
Werkstoffe D-SUB Stift 15pol.:**

Insulator/
Isolierkörper: PA 66 GF UL 94 V-0

Shell/
Gehäuse: Steel, Sn over Ni

Crimp contact/
Crimpkontakt: Copper alloy, Au over Ni


**Contact assignment/
Kontaktbelegung:**

D-Sub

1	black/schwarz
2	brown/braun
3	red/rot
4	pink/rosa
5	yellow/gelb
6	green/grün
7	blue/blau
8	violet/violett
9	grey/grau
10	white/weiss
11	grey pink/grau rosa
12	red blue/rot blau
13	white green/weiss grün
14	brown green/braun grün
15	white yellow/weiss gelb

Shielding
cable strain relief/
Schirmauflage
Zugentlastung

Part no/ Art.-Nr.:	Length L/ Länge L:	Cable/ Kabel:
16-512390	1,8 m	PVC, grey/grau, 15x0,25 mm ² , LiY-CY Cable/Kabel: 781-GN21500
16-512400	3 m	
16-512410	5 m	

				dim. in mm		D-Sub Male 15pol. in SnapLock hood with cable and mounting material	
		drawn/ gez.	Date/Datum	Name		<i>D-Sub Stift 15pol. in SnapLock Haube mit Kabel und Befestigungsmaterial</i>	
		appd./ gepr.	26.11.2024	Lehmenkühler			
			02.12.2024	Koch			
Index: a Original		scale/maßstab: 2:1			dwg no / Z.-nr.: 16K1A4395		DIN- A3
ROHS compliant, exemption 6c <i>ROHS konform, Ausnahme 6c</i>					Customer specific product		1 / 1