




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D1	REVISED AS PER ECR-25-247090	11JUN2025	MDP	DR

- 1
- STAMP AMP 22-18* APPROX AS SHOWN
- 2
- WIRE INSULATION DIA 4.32 [.170] MAX
- 3
- TONGUE MATERIAL THK 0.76±0.05 [.030±.002]

AMP WIRE RANGE
22-18 AWG STRANDED

	50	LOOSE PIECE	8-55846-2
OBSOLETE	1000	LOOSE PIECE	55846-1
	QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 125° C MAX		THIS DRAWING IS A CONTROLLED DOCUMENT.		TE TE Connectivity					
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: 600V MAX (BUILDING WIRING) 1000V MAX (FIXTURES & SIGNS)	DIMENSIONS: mm [INCHES]	0 PLC ± - 1 PLC ± - 2 PLC ± 0.20[.008] 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD B BARE PRODUCT SPEC	NAME TERMINAL, RING TONGUE, SEALABLE HEAT SHRINKABLE —				
	FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 0.26-0.96² [509-1900] STRANDED		MATERIAL BODY: ETP COPPER INSULATION: POLYOLEFIN COLOR: RED		FINISH EDP TIN PLATED	APPLICATION SPEC 408-4022	SIZE A3	CAGE CODE 00779
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.				WEIGHT 0.000000	CUSTOMER DRAWING		SCALE NTS	SHEET 1 OF 1	REV D1