

10		9		8		7		6		5		4		3		2		1				
ITEM	MOLEX P/N	DESCRIPTION			QTY	UOM											FROM	TO	WIRE SIZE	WIRE TYPE	COLOR	
A,B	2064610600	Micro-Fit Plus Rcpt Hsg 2X3			2	PC											A-1	B-1	20 AWG	UL 1061	BLACK	
C	2064620300	Micro-Fit Plus TPA 2X3			4	PC											A-2	B-2	20 AWG	UL 1061	BLACK	
D	2064600021	Micro-Fit Plus FemCrpTer 20-24AWG Tin Lu			12	PC											A-3	B-3	20 AWG	UL 1061	BLACK	
PL	-	PART ID LABEL			1	PC											A-4	B-4	20 AWG	UL 1061	BLACK	
																		A-5	B-5	20 AWG	UL 1061	BLACK
																		A-6	B-6	20 AWG	UL 1061	BLACK

TABLE 1		
LABEL ID	LABEL CONTENT	REMARK
PL	MOLEX PN MOLEX BATCH WK/YR	LABEL TEXT MUST BE 2MM MAX IN HEIGHT WITH ARIAL FONT AND WRAPPED IN FLAG TYPE ON A SINGLE WIRE.

TABLE		
FG PART #	L1	TITLE
2283631062	150±5	Micro-Fit Plus R-R 6Ckt 150mmdisc Sn
2283631064	500±5	Micro-Fit Plus R-R 6Ckt 500mmdisc Sn

NOTE:

1. CONNECTOR VIEW/CIRCUIT NOS SHOWN FROM THE MATING SIDE OF THE CONNECTOR, CONNECTOR VIEW IS SHOWN ONLY FOR REFERENCE. .

2. THE PRODUCT HAS TO MEET PERFORMANCE SPECIFICATION AS PER ES-36586-004.

TESTING REQUIREMENT		
TEST NAME/COMPONENT NAME	TEST PARAMETER	REQUIREMENT
Continuity/Short/Open	AS PER PIN OUT TABLE	100%

DOCUMENT STATUS	P1	RELEASE DATE	2024/11/21	05:44:06
-----------------	----	--------------	------------	----------

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC:		molex SEE TABLE PRODUCT CUSTOMER DRAWING	

</