

10		9		8		
ITEM	MOLEX P/N	DESCRIPTION		QTY	UOM	
A	2064610800	Micro-Fit Plus Rcpt Hsg 2X4		1	PC	
B	2064620400	Micro-Fit Plus TPA 2X4		2	PC	
C	2064600031	Micro-Fit Plus FemCpTer 18AWG Tin Lu		8	PC	
D	-	LEAD FREE SOLDER BAR SAC 305		AR	KG	
PL	-	PART ID LABEL		1	PC	

	2		1	
FROM	TO	WIRE SIZE	WIRE TYPE	COLOR
A-1	-	18 AWG	UL 1061	BLACK
A-2	-	18 AWG	UL 1061	BLACK
A-3	-	18 AWG	UL 1061	BLACK
A-4	-	18 AWG	UL 1061	BLACK
A-5	-	18 AWG	UL 1061	BLACK
A-6	-	18 AWG	UL 1061	BLACK
A-7	-	18 AWG	UL 1061	BLACK
A-8	-	18 AWG	UL 1061	BLACK

TABLE 1		
LABEL ID	LABEL CONTENT	REMARK
PL	MOLEX PN MOLEX BATCH WK/YR	LABEL TEXT MUST BE 2MM MAX IN HEIGHT WITH ARIAL FONT AND WRAPPED IN FLAG TYPE ON A SINGLE WIRE.




TABLE		
FG PART #	L1	TITLE
2284111082	150±5	Micro-Fit Plus R-S 8ckt 150mmdisc Sn
2284111083	300±5	Micro-Fit Plus R-S 8ckt 300mmdisc Sn

NOTE:

1. CONNECTOR VIEW/CIRCUIT NOS SHOWN FROM THE MATING SIDE OF THE CONNECTOR, CONNECTOR VIEW IS SHOWN ONLY FOR REFERENCE. .
2. THE PRODUCT HAS TO MEET PERFORMANCE SPECIFICATION AS PER ES-36586-004.
3. FREE ENDS MUST BE STRIPPED, TWISTED & TINNED. TINNING DIA MUST BE 1.39MM MAX.

TESTING REQUIREMENT		
TEST NAME/COMPONENT NAME	TEST PARAMETER	REQUIREMENT
Continuity/Short/Open	AS PER PIN OUT TABLE	100%

A	INITIAL RELEASE	804816	20/11/2024
REVISION	CHANGE NOTE	EC NO	DATE
REVISION HISTORY			

[illegible]

DOCUMENT STATUS	P1	RELEASE DATE	2024/11/21 05:44:08
-----------------	----	--------------	---------------------