








Section A-A



PCB Layout



LF Contacts number	Distance in mm between axes		Length in mm	LF Contacts reference mark number			
	A	B		D	E	F	G
XXX	A	B	C	I	2	3	4
004	1,27	8,27	12,87	I	3	4	6
006	2,54	9,54	14,14	I	4	5	8
008	3,81	10,81	15,41	I	5	6	10
010	5,08	12,08	16,68	I	6	7	12
012	6,35	13,35	17,95	I	7	8	14
014	7,62	14,62	19,22	I	8	9	16
016	8,89	15,89	20,49	I	9	10	18
018	10,16	17,16	21,76	I	10	11	20
020	11,43	18,43	23,03	I	11	12	22
022	12,7	19,7	24,3	I	12	13	24
024	13,97	20,97	25,57	I	13	14	26
026	15,24	22,24	26,84	I	14	15	28
028	16,51	23,51	28,11	I	15	16	30
030	17,78	24,78	29,38	I	16	17	32
032	19,05	26,05	30,65	I	17	18	34
034	20,32	27,32	31,92	I	18	19	36
036	21,59	28,59	33,19	I	19	20	38
038	22,86	29,86	34,46	I	20	21	40
040	24,13	31,13	35,73	I	21	22	42
042	25,4	32,4	37	I	22	23	44
044	26,67	33,67	38,27	I	23	24	46
046	27,94	34,94	39,54	I	24	25	48
048	29,21	36,21	40,81	I	25	26	50
050	30,48	37,48	42,08	I	26	27	52
052	31,75	38,75	43,35	I	27	28	54
054	33,02	40,02	44,62	I	28	29	56
056	34,29	41,29	45,89	I	29	30	58
058	35,56	42,56	47,16	I	30	31	60
060	36,83	43,83	48,43	I			

Notes:

- 1 - "XXX" to be replaced by the number of LF contacts.
- 2 - Connector delivered with part 1 & 2 of the fittings not assembled and part 3 & 4 of the fittings assembled.
- 3 - General tolerance $\pm 0,2$

MICRO HDAS
Male connector
MHDAS 2 M XXX YC E63

EXPORT CONTROL CLASSIFICATION NOT CONTROLLED/EAR99

Information contained in this document is not subject to Export Control Regulations of the European Union, USA or other countries. Each recipient of this document is responsible for ensuring that transfer or use of any information contained in this document complies with all relevant Export Control regulations and EAR99 regulations.

DRAWN BY : A Samanta

UPDATED BY : -

LAST APPROVED BY : M Gervais

ALL DIMENSIONS ARE IN MM

SCALE : 7



AMPHENOL SOCAPEX

B.P. 29 74311 THYEZ CEDEX

ORIGINAL DRAWING DATE : 25/06/2024

CONFIGURATION DATA ARE AVAILABLE IN PDM

REV : A

PAGE : 1/1

169-PLC-1826-00