






NOTES: UNLESS OTHERWISE SPECIFIED

1. MATERIALS AND FINISH
 - 1.1 BODY: GOLD PLATED BRASS
 - 1.2 CENTER CONTACT: GOLD PLATED BERYLLIUM COPPER
 - 1.3 INSULATOR: PTFE
2. ELECTRICAL SPECIFICATIONS
 - 2.1 FREQUENCY RANGE: DC TO 18 GHz
 - 2.2 IMPEDANCE: 50 OHMS NOMINAL
 - 2.3 VSWR (MAXIMUM): 1.2 : 1

	3RD ANGLE PROJECTION 	MIDWEST MICROWAVE		
NOTICE: The information in this drawing is PROPRIETARY and must not be used without the permission of Cinch Connectivity Solutions. It may contain data whose export is restricted. Verify status prior to exporting. INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2018	RoHS2 ☒ 2015/863/EU UNLESS OTHERWISE SPECIFIED UNITS: INCH	Title: SMA FEMALE TO FEMALE ADAPTOR		
	.XX ±.02 FRACTIONS ±1/64 ANGLES ±2°	Model No.: CGM-1180-FF-SMA-09 Size: A DO NOT SCALE DRAWING Date: 05/21/2021 Sheet: 1 OF 1		