








10167523-XXXXLF



PART NO.	A	B	C	D	E	F
10167523-1212LF	15.00	8.25	16.50	18.80	19.85	10.00
10167523-0606LF	6.00	3.75	7.50	9.80	10.85	10.00

spec ref -				dr	Premchand, Pra	2023/03/15			size	A3	scale	3:1
tolerance std ISO 406 ISO 1101 TOLERANCES UNLESS OTHERWISE SPECIFIED				eng	Premchand, Pra	2024/06/16			ecn no	ELX-I-48871-1		
				chr	-	-						
				appr	Paul Mithun	2024/06/16	product family - MINITEK PWR			rel level	Released	
surface ISO 1302	linear	0.X	±.25	Amphenol FCI	title CABLE HOUSING PICPWR OCP			dwg no	10167523 ptc_wm - E			
		0.XX	±.20									
		0.XXX	±--									
					cat. no.	-	Product - Customer Drw			sheet 1 of 2		

VIEW OF 12 POSITION RECEPTACLE HOUSING



NOTE:

- 1. MATERIAL : NYLON, PA66 UNFILLED
UL94V-0, HALOGEN FREE
COLOUR : BLACK, GLOW WIRE COMPATIBLE
- 2. USED WITH AICC POWER TERMINAL 10167522, 10174057
- 3. USED WITH AICC SIDEBAND TERMINAL 10167521
- 4. MATES WITH AICC HEADER 10167519, 10167520.
- 5. PRODUCT SPECIFICATION : GS-12-1766
- 6. PACKAGE SPECIFICATION : GS-14-3016
- 7. APPLICATION SPECIFICATION : GS-20-0807
- 8. PART NUMBER LOGIC

10167523-XX XX LF

NO. OF POWER POSITIONS

12 → 12 PINS
06 → 06 PINS

NO. OF SIGNAL POSITIONS

12 → 12 PINS
06 → 06 PINS

Amphenol
FCi

© 2020 Amphenol Corporation

spec ref -				dr	Premchand, Pra	2023/03/15	<div>projection</div> <div></div>	<div>MM</div> <div></div>	size	A3	scale	3:1
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED		eng	Premchand, Pra	2024/06/16			ecn no ELX-I-48871-1			
ISO 406 ISO 1101				chr	-	-						
				appr	Paul Mithun	2024/06/16	product family - MINITEK PWR		rel level Released			
<div>surface</div> <div></div> <div>ISO 1302</div>	linear	0.X	±.25	Amphenol FCi	title CABLE HOUSING PICPWR OCP			dwg no	10167523		rev	
		0.XX	±.20									
		0.XXX	±--									
	angular	0°	±--°	cat. no.	-	Product - Customer Drw			sheet 2 of 2			
p t c _ w m - B												