




Amphenol
FCI
© 2016 AFCE




NOTE:
1.MATERIAL:PHOSPHOR BRONZE
2.FINISH
CONTACT AREA:REFER TO ORDERING CODE
CRIMPING AREA:GOLD FLASH FOR GOLD PLATED
TIN FOR TIN PLATED
3.MATE WITH HOUSING:AFCE 10157097/10164367
4.OPERATING TEMPERATURE: -40°C~+105°C
5.WIRE SIZE:AWG#28~32, INSULATION O.D.:0.8MM MAX
6.ORDERING CODE:10157098-X 0 1 LF


FINISH
0:BRIGHT TIN PLATING
1:GOLD FLASH
2:15u" MIN GOLD
3:30u" MIN GOLD



SECTION: A-A
SCALE: 1:1



SECTION: B-B
SCALE: 1:1



mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection mm	product family FITMATE			
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm	title 1.00mm pitch connector Terminal			
A	NEW RELEASE	YS	2022-08-17	angles	.X±.50					
B	ELX-N-54337	JH	2024/12/27	linear	.XX±.25					
				0'±x'	.XXX±.10	scale 2:1				
				dr	Jason.Wang	2020-3-3	Amphenol FCI	dwg no		sheet 1 of 1
				enr	Jason.Wang	2020-3-3		10157098		A3
				chr	Song.Yang	2022-08-17		type Product Customer Drawing		
				app	Tim.Yao	2022-08-17				
sheet index	revision	B								
	sheet	1								