



Amphenol FCI



© 2016 AFCI



SECTION: A-A
SCALE: 1:1



SECTION: B-B
SCALE: 1:1




SECTION: C-C
SCALE: 1:1

- NOTE:
- 1.MATERIAL: PHOSPHOR BRONZE
 - 2.PRODUCT SPEC:
PRODUCT SPECIFICATION GS-12-1572
 - 3.VOLTAGE RATING: 50V AC/DC. CURRENT RATING: 1A AC/DC
 - 4.TEMPERATUR RANGE: -40°C~+105°C
 - 5.USE WITH HOUSING: 10155244
 - 6.WIRE SIZE: AWG#26~30
 - 7.INSULATION ϕ O.D.: 1.00mm MAX
 - 8.ORDERING CODE: 10155245-X 1 LF

LEAD FREE

FINISHA
1: GOLD FLASH
2: BRIGHT TIN PLATING



mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family FitMate			
ltr	ecn no	dr	date	tolerances unless otherwise specified			mm 		title 1.25mm pitch connector crimp terminal				
A	New Released	Jason	2019-10-21	angles	linear	.X±.3		Amphenol FCI					
B	ELX-N-55541	CP	2025/04/22			.XX±.20							
				.XXX±.10		scale 4:1							
				dr	Jason Wang	2019-10-21		dwg no		sheet 1 of 5		size	
				engr	Jason Wang	2019-10-21		10155245				A3	
				chr	-	-							
				appd	TIM YAO	2019-10-21		type		Product Customer Drawing			
sheet index	revision	B											
	sheet	1											