



ASSY P/N	GROMMET SIZE
W3B82-7SG-P-535	GROMMET ID .375 [9.5] FOR CABLE OD .350-.400 [8.9-10.2]

NOTES:

1. PARTS TO BE BULK PACKED.
2. SOLDER CONTACTS ARE PRESSED INTO CONNECTOR WITH ALL CONTACTS FACING AWAY FROM KEY (DOWN).
3. ALL DIMENSIONS ARE FOR REFERENCE ONLY EXCEPT WHERE NOTED WITH TOLERANCE.

**FACE VIEW**

CABLE CONNECTOR, FEMALE
MAT'L: UV PBT, BLACK
COUPLING RING
MAT'L: UV PBT, BLACK
O-RING
MAT'L: SILICONE, RED
SPRING
MAT'L: STAINLESS STEEL



(3) #12 SOCKET CONTACT
SOLDER CUP STYLE
MAT'L: COPPER ALLOY
GOLD PLATED

(4) #26 SOCKET CONTACT
SOLDER CUP STYLE
MAT'L: COPPER ALLOY
GOLD PLATED

(2) #4 SCREW
MAT'L: STAINLESS STEEL

BACKSHELL STRAP
MAT'L: UV NYLON, BLACK

.430
[10.9]



.378
[9.6]

1.030
[26.2]

SLEEVE
MAT'L: UV PBT, BLACK

BACKSHELL
MAT'L: UV PBT, BLACK

GROMMET
MAT'L: RUBBER, BLACK

**WIRE VIEW****SHOWN ASSEMBLED**
FOR CUSTOMER REF ONLY

DIMENSIONS IN BRACKETS [] ARE METRIC.

CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: _____
DATE: _____

RoHS COMPLIANT

A	MA	09-26-24	RELEASED PER PDR 20013-9	
	AB	03-22-24	O-RING WAS 6290S-1; P-20013-9	
		09-03-21	CHANGED TO ALL SOLDER CUPS FACING DOWN; P-20013-6	
		04-19-21	DRAWING CREATED PER PDR 20013	
REV.	INIT.	DATE	DESCRIPTION	
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION". UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			ORIG. DRAWN BY: AB	DATE: 04-19-21
			CHECKED BY:	
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS.			APPROVED BY:	
			TITLE: CABLE END CONNECTOR KIT (3) #12 + (4) #26 SKT CONTACTS, SOLDER CUP MULTI-CON-X, W.R. INSTA-CLICK™	
FILE: W3B82-7SG-P-5XX			SCALE: NTS	SHEET: 1 OF 1
DIRECTORY: SLW			CUSTOMER: STANDARD PRODUCT	
PART NUMBER: W3B82-7SG-P-5XX			REV A	