



- NOTES:**
- PARTS TO BE BULK PACKED.
 - SOLDER CONTACTS ARE PRESSED INTO CONNECTOR WITH ALL CONTACTS FACING AWAY FROM KEY (DOWN).
 - ALL DIMENSIONS ARE FOR REFERENCE ONLY EXCEPT WHERE NOTED WITH TOLERANCE.




STD COUPLING RING
P/N: W3B82-7PG-3XX



WINGED COUPLING RING
P/N: W3B82-7PG-3XXW

ASSY P/N	GROMMET SIZE
W3B82-7PG-335	GROMMET ID .375 [9.5] FOR CABLE OD .350-.370 [8.9-9.4]
W3B82-7PG-335W	



CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: _____
DATE: _____

A	MA	09-10-24	RELEASED PER PDR 20013-3
	AB	06-04-21	CHANGED TO ALL SOLDER CUPS FACING DOWN; P-20013-3
		03-23-21	DRAWING CREATED PER PDR 20013
REV.	INIT.	DATE	DESCRIPTION
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION". UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.		ORIG. DRAWN BY: AB	DATE: 03-23-21
		CHECKED BY:	
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS.		APPROVED BY:	
		TITLE: CABLE END CONNECTOR KIT (3) #12 + (4) #26 PIN CONTACTS, SOLDER CUP MULTI-CON-X, WEATHER RESISTANT CUSTOMER: STANDARD PRODUCT	
FILE: W3B82-7PG-3XX	SCALE: NTS	SIZE: B	SHEET: 1 OF 1
	DIRECTORY: SLW	PART NUMBER: W3B82-7PG-3XX(W)	REV: A

DIMENSIONS IN BRACKETS [] ARE METRIC.

RoHS COMPLIANT