



- NOTES:**
1. PARTS TO BE BULK PACKED.
 2. SOLDER CONTACTS ARE PRESSED INTO CONNECTOR WITH ALL CONTACTS FACING AWAY FROM KEY (DOWN).
 3. ALL DIMENSIONS ARE FOR REFERENCE ONLY EXCEPT WHERE NOTED WITH TOLERANCE.




STD COUPLING RING
P/N: W3B82-7SG-3XX



WINGED COUPLING RING
P/N: W3B82-7SG-3XXW

ASSY P/N	GROMMET SIZE
W3B82-7SG-335	GROMMET ID .375 [9.5] FOR CABLE OD .350-.370 [8.9-9.4]
W3B82-7SG-335W	



CUSTOMER APPROVAL	
THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.	
APPROVED BY:	_____
DATE:	_____

A	MA	09-10-24	RELEASED PER PDR 20013-3
	AB	06-04-21	CHANGED TO ALL SOLDER CUPS FACING DOWN; P-20013-3
		03-29-21	DRAWING CREATED PER PDR 20013
REV.	INIT.	DATE	DESCRIPTION
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION". UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.		ORIG. DRAWN BY: AB	DATE: 03-29-21
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS.		CHECKED BY:	
APPROVED BY:		FILE: W3B82-7SG-3XX(W)	DIRECTORY: SLW
SCALE NTS		SIZE B	SHEET 1 OF 1
TITLE: CABLE END CONNECTOR KIT (3)#12 + (4)#26 SKT CONTACTS, SOLDER CUP MULTI-CON-X, WEATHER RESISTANT STANDARD PRODUCT		PART NUMBER: W3B82-7SG-3XX(W)	REV A

DIMENSIONS IN BRACKET [] ARE METRIC.

RoHS COMPLIANT

▷ = CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX