




ASSY P/N	GROMMET SIZE
W3B80-7PG-P-335	GROMMET ID .375 [9.5] FOR CABLE OD .350-.370 [8.9-9.4]



- NOTES:**
1. PARTS TO BE BULK PACKED.
 2. CONTACTS ARE SUPPLIED UNASSEMBLED.
 3. ALL DIMENSIONS ARE REFERENCE EXCEPT WHERE NOTED WITH TOLERANCE.

**FACE VIEW**


CABLE CONN, MALE
MAT'L: UV PBT, BLACK
COUPLING RING
MAT'L: UV PBT, BLACK
O-RING
MAT'L: SILICONE, RED
SPRING
MAT'L: STAINLESS STEEL



(3) #12 PIN CONTACT
CRIMP STYLE
MAT'L: COPPER ALLOY
GOLD PLATED





GROMMET
MAT'L: RUBBER,
BLACK



SLEEVE
MAT'L: UV PBT, BLACK

BACKSHELL
MAT'L: UV PBT, BLACK

**WIRE VIEW****ASSEMBLED VIEW**
FOR CUSTOMER REF ONLY

DIMENSIONS IN BRACKETS [] ARE METRIC.

CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: _____
DATE: _____

RoHS COMPLIANT

A	MA	09-18-24	RELEASED PER PDR 20013-9	
	AB	03-22-24	O-RING WAS 6290S-1; P-20013-9	
		04-20-21	DRAWING CREATED PER PDR 20013; P-20013-6	
REV.	INIT.	DATE	DESCRIPTION	
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION". UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			ORIG. DRAWN BY: AB	DATE: 04-20-21
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS.			CHECKED BY:	 601 E. WILDWOOD VILLA PARK, IL 60181
			APPROVED BY:	
			SCALE: NTS SIZE: B SHEET: 1 OF 1	
FILE: W3B80-7PG-P-3XX			DIRECTORY: SLW	PART NUMBER: W3B80-7PG-P-3XX
= CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX			TITLE: CABLE END CONNECTOR KIT (3) #12 + (4) #26 PIN CONTACTS, CRIMP MULTI-CON-X, WEATHER RESISTANT STANDARD PRODUCT	
			REV A	