


10		9		8		7	
ITEM	MOLEX P/N	DESCRIPTION				QTY	UOM
A	2207182001	6.0MM HYPERQUBE PLUG HSG, NATURAL				1	PC
B	2207191002	6.0MM HYPERQUBE MALE CRIMP CONTACT, 4AWG				1	PC
PL	-	PART IDENTIFICATION LABEL 100X15				1	PC

FROM	TO	WIRE TYPE	WIRE SIZE	COLOR
A-1	--	UL 3614	4 AWG	BLACK

TABLE 1		
LABEL ID	LABEL CONTENT	REMARKS
PL	MOLEX PN MOLEX BATCH WK/YR	LABEL TEXT MUST BE 2MM MAX IN HEIGHT WITH ARIAL FONT AND WRAP AROUND WIRE.



NOTE:

1. CONNECTOR VIEW/CIRCUIT NOS SHOWN FROM THE MATING SIDE OF THE CONNECTOR, CONNECTOR VIEW IS SHOWN ONLY FOR REFERENCE.
2. THE FREE ENDS TO BE STRIPPED AND RETAINED.



PRODUCT REQUIREMENT		
TEST NAME/COMPONENT NAME	TEST PARAMETER	REQUIREMENT
CONTINUITY/SHORT/OPEN	AS PER PIN OUT TABLE	TO BE MET

CSR

A1	LABEL ORIENTATION IS UPDATED	ER	08/APR/2025	NA	NA
A	INITIAL RELEASE	815809	13/MAR/2025	NA	NA
REVISION	CHANGE NOTE	EC NO	DATE	CUSTOMER P/N	CUSTOMER REV

REVISION HISTORY	
------------------	--

[illegible]

DETAIL	DESCRIPTION	DETAIL	DESCRIPTION
	Continues Taping		PVC sleeve or Silicon sleeve
	HST		T Dimension
	Woven Braid		Convuluted Tube
	Spot Taping		Customer Specific requirements

DOCUMENT STATUS	P1	RELEASE DATE	2025/04/09	08:21:19
-----------------	----	--------------	------------	----------