



SPECIFICATIONS:

- CONTACT RESISTANCE: 20m OHM MAX.
- INSULATION REISTANCE: 300M OHM MIN. AT DC 500V.
- VOLTAGE WITHSTANDING: AC 1000V FOR ONE MIN.
- INSERTION FORCE: 4.0KG MAX.
- WITHDRAWAL FORCE: 1-3.5KG.
- RATING: 100V A.C. AT 2A

JIN RUH CO., LTD			
TOLERANCES		PART NUMBER	
.X ± /	.XXX ± /	JR 2712	
.XX ± /	ANGLES /		
	mm	SCALE	DESCRIPTION
DRAFT W.RAY 052303			DIN SOCKET
CHECK JANNE HUNG		REV.	A
APPROVAL DANNY HSU		SHEET	1/1