



DATE	REV	DESCRIPTION	BY	CHKD



orange 1 white/orange	green 2 white/green
blue 3 white/blue	brown 4 white/brown


lead	<1000ppm
Cadmium	<100ppm
Mercury	<1000ppm
Chromium	<1000ppm
PBB	<1000ppm
PBDE	<1000ppm

Material:ROHS compliant from OCT.2004

PA/R	PINOUT		
	P1 (T568B)	WIRE	P2
1	1	WHT/ORG	3
	2	ORG	6
2	3	WHT/GRN	1
	6	GRN	2
3	4	BLU	7
	5	WHT/BLU	8
4	7	WHT/BRN	4
	8	BRN	5

Conductor	Rare Copper 26AWG 70.15±0.15mm
Insulation	ThicknessMIN at any point0.15mm MAX AVG0.25mm Diameter0.92±0.05mm
Jacketing	PVC ThicknessMIN at any point0.50mm MAX AVG0.60mm Diameter5.6±0.2mm

WIRE	CAT. 5E FTP STR
Plug	YS-02
Length	3M
COLOR	GY825



Unless specified on the drawing, tolerances are per the follows:

.	± 1
.X	± 0.2
.XX	± 0.05

3RD



DRAW.NO	YS-02	ITEM	1962-3X		
DEPARTMENT		DRAW	Peace Jing	DATE	2006/02/27
SCALE		CHECKER		APPROVAL	
UNIT	MM	SHEET	1	OF	1