




- ① MOLDED PARTS: FLAME RETARDANT 94V-0 RATED THERMOPLASTIC, BLACK.
SHELL: CARBON STEEL
CONTACTS: PHOSPHOR BRONZE
EYELETS: BRASS
SCREWLOCKS: ZINC
INSERTS: ZINC
- ② SHELL: .000100 MIN TIN OVER .000050 MIN COPPER.
CONTACTS: SEE TABLE
EYELETS: .000100 MIN TIN OVER COPPER FLASH.
SCREWLOCKS: CLEAR CHROMATE
INSERTS: CLEAR CHROMATE
- ③ GOLD FLASH FOR A DISTANCE OF .100 MIN FROM
MATING END, .000100 MIN TIN
ON OPPOSITE END, ALL OVER .000050 MIN NICKEL.
- ④ .000030 MIN GOLD FOR A DISTANCE OF .100 MIN FROM
MATING END, .000100 MIN TIN
ON OPPOSITE END, ALL OVER .000050 MIN NICKEL.

FEMALE SCREWLOCKS	$\frac{4}{3}$	5745783-6
FEMALE SCREWLOCKS	$\frac{3}{5}$	5745783-5
THREADED INSERTS	$\frac{4}{4}$	5745783-4
THREADED INSERTS	$\frac{3}{5}$	5745783-3
NONE	$\frac{4}{4}$	5745783-2
MOUNTING HARDWARE	CONTACT FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN 04-06-05 A. FERNANDEZ-DOCKS CHK 04-06-05 S. BOLASH APVO 04-06-05 M. WALMSLEY		tyco <i>Electronics</i> Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
INCHES		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± 2°		RCPT ASSY, SIZE 3, 25 POSN, RTANG. AMPULMITE HD-20, WITH METAL SHELL, WITH OR WITHOUT SCREWLOCKS OR INSERTS	
		PRODUCT SPEC 108-40025 APPLICATION SPEC 114-40010		SIZE A1	
MATERIAL		FINISH		CAGE CODE	
1		2		DRAWING NO	
				00779	
				C-5745783	
				SCALE	
				4:1	
				SHEET	
				1 OF 1	
				REV	
				0	
				CUSTOMER DRAWING	