


RECOMMENDED P.C. BOARD HOLE-LAYOUT



DO NOT SCALE METRIC THIRD ANGLE PROJECTION

ACCESSORIES PREFIX "Z"	ITEM NR.	DESCRIPTION OF ACCESSORY	2	2	2	2	2	2	2
5		BUSHING WITH THROUGH HOLE 3,1 DIA.							
5		BUSHING WITH INNER THREAD 4-40 UNC							
5		BUSHING WITH INNER THREAD M3							
4		FEMALE SCREWLOCK WITH 4-40 UNC							
4		FEMALE SCREWLOCK WITH M3							
7		BOARDLOCK							

HOW TO ORDER:  
 9 POS.-----> Z-106505-Y  
 PREFIX FOR ACCESSORIES }  
 BASIC PARTNR. }  
 SUFFIX FOR PLATING }

PLATING SUFFIX "Y"	0	1	2	3	4	5	6	7	8	9
	XXXXXX-Y	XXXXXX-Y	XXXXXX-Y	XXXXXX-Y	XXXXXX-Y	XXXXXX-Y	XXXXXX-Y	XXXXXX-Y	XXXXXX-Y	XXXXXX-Y

GOLD OVER NICKEL AS PER PERFORMANCE LEVEL 2 (DIN 41652)  
 SOLDERPART : 2,5µm TIN OVER NICKEL } -Y = -2

NOTES :  
 ① GROOVE INDICATES VERSION WITH 4-40 UNC INNER THREAD; WITHOUT GROOVE INDICATES VERSION WITH M3 INNER THREAD.  
 ② CAVITY IDENTIFICATION AT FRONT SIDE ONLY.  
 ③ PARTNUMBER AND DATE CODE.

ITEM NRS./MATERIAL :

① SHELL	: BRIGHT TINPLATED STEEL
② HOUSING	: GLASSFILLED POLYESTER, COLOR : BLACK
③ CONTACTS	: PHOSPHORBRONZE (PLATING : SEE TABLE ABOVE)
④ FEMALE SCREWLOCK	: TINPLATED STEEL (INNER THREAD 4-40 UNC OR M3)
⑤ BUSHING	: TINPLATED STEEL (INNER THREAD 4-40 UNC OR M3 OR 3,1 DIA THRU-HOLE)
⑥ BRACKET	: TINPLATED STEEL
⑦ BOARDLOCK	: TINPLATED PHOSPHORBRONZE
⑧ POST ALIGNMENTPLATE	: GLASSFILLED NYLON COLOR : BLACK

CUSTOMER DRAWING				FOR REFERENCE ONLY WILL NOT BE UPDATED	
© COPYRIGHT 19- BY AMP-HOLLAND B.V. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING.					
THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION					
H	EHCO-0061-04	JvdH	PDJ	07 APR 04	NAME
G	EH-0033-99	D.K.	W.S.	14 JAN 99	HD-20 SIZE 1 RIGHT ANGLE RECEPTACLE HEADER; MARK II*
LTR.	REVISION RECORD	DR.	CHK.	DATE	
DR.:	D. KESSLER	CHK.:	W. SOOMERS	APP.:	-
DATE:	14 JAN 99	DATE:	-	DATE:	-
DWG.No.	C-106505	REV.LTR.	H	SHEET	1 OF 1
					A2