


RECOMMENDED P.C. BOARD HOLE-LAYOUT



DO NOT SCALE METRIC THIRD ANGLE PROJECTION

DIMENSIONS IN mm		2		2		2		2		2	
5	BUSHING WITH THROUGH HOLE 3,1 DIA.										
5	BUSHING WITH INNER THREAD 4-40 UNC										
5	BUSHING WITH INNER THREAD M3										
4	FEMALE SCREWLOCK WITH 4-40 UNC										
4	FEMALE SCREWLOCK WITH M3										
7	BOARDLOCK										

ITEM NR.	DESCRIPTION OF ACCESSORY										
	25 POS.-----> Z-106507-Y										
	PREFIX FOR ACCESSORIES	0-XXXXXX-Y	1-XXXXXX-Y	2-XXXXXX-Y	3-XXXXXX-Y	4-XXXXXX-Y	5-XXXXXX-Y	6-XXXXXX-Y	7-XXXXXX-Y	8-XXXXXX-Y	9-XXXXXX-Y
	BASIC PARTNR.										
	SUFFIX FOR PLATING										

PLATING SUFFIX-Y	
	GOLD OVER NICKEL AS PER PERFORMANCE LEVEL 2 (DIN 41652)
	SOLDERPART : 2,5µm TIN OVER NICKEL
	-Y = -2
	-
	-

NOTES :  
 ① GROOVE INDICATES VERSION WITH 4-40 UNC INNER THREAD; WITHOUT GROOVE INDICATES VERSION WITH M3 INNER THREAD.  
 ② CAVITY IDENTIFICATION AT FRONT SIDE ONLY.  
 ③ PARTNUMBER AND DATE CODE.

ITEM NRS./MATERIAL :

① SHELL	: BRIGHT TINPLATED STEEL
② HOUSING	: GLASSFILLED POLYESTER, COLOR : BLACK
③ CONTACTS	: PHOSPHORBRONZE (PLATING : SEE TABLE ABOVE)
④ FEMALE SCREWLOCK	: TINPLATED STEEL (INNER THREAD 4-40 UNC OR M3)
⑤ BUSHING	: TINPLATED STEEL (INNER THREAD 4-40 UNC OR M3 OR 3,1 DIA THRU-HOLE)
⑥ BRACKET	: TINPLATED STEEL
⑦ BOARDLOCK	: TINPLATED PHOSPHORBRONZE
⑧ POST ALIGNMENTPLATE	: GLASSFILLED NYLON, COLOR : BLACK

CUSTOMER DRAWING				FOR REFERENCE ONLY WILL NOT BE UPDATED			
© COPYRIGHT 19- BY AMP-HOLLAND B.V. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING.							
THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION							
H EHCO-0061-04 JvdH PDJ 07 APR 04				NAME HD-20 SIZE 3			
G EH-0033-99 D.K. W.S. 14 JAN 99				RIGHT ANGLE RECEPTACLE HEADER; MARK II*			
LTR.	REVISION RECORD	DR.	CHK.	DATE	DWG.No.	REV.LTR.	SHEET
					C-106507	H	1 OF 1