


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
IJ	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
		A		INITIAL ISSUE	10 SEP 05	MGR	DB
		A1		REVISED PER ECO-10-002850	10FEB10	KK	HMR



NOTES:

- 1 ATTENUATION $\leq 0,3$ dB, MEASURED AT 1300nm ACC. TO IEC 61300-3-4 EQUILIBRIUM MODE CONDITION
- 2 SUPPLY FILLED OUT TEST RESULT SHEET WITH EACH INDIVIDUALLY PACKED ASSEMBLY
- 3 CABLE INFO:
 CORE DIA - 62,5/125 μ m
 OUTER DIA - 2,5 mm
 JACKET COLOR - ORANGE
 JACKET MATERIAL - LSZH

4 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
 5349573-7, 5349573-8, 5349573-9, 5-5349573-0, 8-5349573-1

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (Meter)
X-5349573-Y	XY,0
9-5349573-1	1,5
9-5349573-8	15,5
9-5349573-9	9,5
0-5349573-0	100,0

Qty	Part Number	Description	Item
1	-	TEST RESULT SHEET	-
2	-	PROTECTIVE COVER, 2.5MM, BLACK	5
2	-	KIT, MM, CER, ASSY, BULK	4
2	-	CRIMP EYELET, BRIGHT TIN	3
2	-	FOAC STRAIN RELIEF 2,5 BAY BLACK	2
L	-	FOCAB 62.5/125 SIMPLEX, ORANGE	1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN GIRIYAPPA. M 10 SEP 05	Tyco Electronics Corporation Tyco Electronics FOBU, Bangalore, India	
DIMENSIONS: mm		CHK DIWAKAR BELAVADI 10 SEP 05	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC \pm - 1 PLC \pm - 2 PLC \pm - 3 PLC \pm - 4 PLC \pm - ANGLES \pm -		APVD DIWAKAR BELAVADI 10 SEP 05	FOMM62,5 LEAD 2,5S ST - ST	
MATERIAL		FINISH	SIZE A2	CAGE CODE 00779
		WEIGHT	DRAWING NO C=5349573	RESTRICTED TO
		CUSTOMER DRAWING	SCALE NTS	SHEET 1 OF 1
			REV A1	