



# SUHNER® COAXIAL CONNECTOR DATA SHEET

## TYPE 24\_MCX-50-1-13/111\_N

### Description

Straight panel bulkhead cable jack, flange mount

**SUHNER full crimp cable attachment**  
**Front mount chassis connector**



### General Information

MCX Interface dims acc. to:  
Weight:

IEC 60169-36\_CECC 22220  
0.0018 Kg / 0.06 oz

### Cable

Cable type:  
Cable type:  
Cable type:

RG\_178B/U  
EF\_178  
RG\_196A/U

### Cable Entry

Centre contact:  
Outer contact:

crimped  
crimped

### Electrical Data

Impedance:  
Interface frequency max.:

50Ω  
6 GHz

### Piece Parts

Center contact:  
Outer contact:  
Body:

### Material

Copper Beryllium Alloy  
Brass  
Brass

### Surface Plating

Gold Plating (Nickel underplated)  
Gold Plating (Nickel underplated)  
Gold Plating (Nickel underplated)

Insulator:

PFA / PTFE

Fastening nut:  
Washer:  
Crimp Ferrule:

Brass  
Bronze  
Copper

Gold Plating (Nickel underplated)  
Gold Plating (Nickel underplated)  
Gold Plating

### Attachments

Outline drawing:  
Catalogue drawing:  
Assembly instruction:

DOU-00008913  
DCA-00008915  
DOC-0000182201

### Notes

Mounting hole:  
Order as **24\_MCX-50-1-13/111\_NH** for Bulk 100 pcs

#### WAIVER!

While the information contained in this folder has been carefully compiled to the best of our present knowledge, it is not intended as representation or warranty of any kind on our part regarding the fitness of the products concerned for any particular use or purpose and neither shall any statement contained herein be construed as a recommendation to infringe any industrial property rights or as a license to use any such rights. The fitness of each product for any particular purpose must be checked beforehand with our specialists.



**HUBER+SUHNER**

HUBER+SUHNER AG  
Interconnect Division  
CH-9100 Herisau  
Phone +41 (0)71 353 41 11  
Fax +41 (0)71 353 45 90  
<http://www.hubersuhner.com>

Issued: 18.12.03 08:51

Document: DOC-0000185080

RF\_Ca\_Pa\_C\_PDF

**uncontrolled copy**

Page 1