



# SUHNER® COAXIAL CONNECTOR DATA SHEET

## TYPE 24\_MCX-50-2-7/111\_N

### Description

Straight panel bulkhead cable jack, flange mount

**SUHNER full crimp cable attachment**  
**Front mount chassis connector**



### General Information

MCX Interface dims acc. to:  
Weight:

IEC 60169-36\_CECC 22220  
0.0014 Kg / 0.05 oz

### Cable

Cable type:  
Cable type:  
Cable type:

EF\_316  
RG\_316U  
RG\_188A/U

### Cable Entry

Centre contact:  
Outer contact:

crimped  
crimped

### Electrical Data

Impedance:  
Interface frequency max.:

50Ω  
6 GHz

### Piece Parts

Center contact:  
Outer contact:  
Body:

### Material

Copper Beryllium Alloy  
Brass  
Brass

### Surface Plating

Gold Plating (Nickel underplated)  
Gold Plating (Nickel underplated)  
Gold Plating (Nickel underplated)

Insulator:

PFA / PTFE

Coupling nut:  
Fastening nut:  
Washer:  
Crimp Ferrule:

PFA / PTFE  
Brass  
Bronze  
Copper

Gold Plating (Nickel underplated)  
Gold Plating (Nickel underplated)  
Gold Plating

### Attachments

Outline drawing:  
Catalogue drawing:  
Assembly instruction:

DOU-00009715  
DCA-00008915  
DOC-0000179868

### Notes

Mounting hole:

DOU-00008855

#### WAIVER!

While the information contained in this folder has been carefully compiled to the best of our present knowledge, it is not intended as representation or warranty of any kind on our part regarding the fitness of the products concerned for any particular use or purpose and neither shall any statement contained herein be construed as a recommendation to infringe any industrial property rights or as a license to use any such rights. The fitness of each product for any particular purpose must be checked beforehand with our specialists.



## HUBER+SUHNER

HUBER+SUHNER AG  
Interconnect Division  
CH-9100 Herisau  
Phone +41 (0)71 353 41 11  
Fax +41 (0)71 353 45 90  
<http://www.hubersuhner.com>

Issued: 18.12.03 08:51

Document: DOC-0000186531

RF\_Ca\_Pa\_C\_PDF


**uncontrolled copy**

Page 1



# SUHNER® COAXIAL CONNECTOR DATA SHEET

Order as **24\_MCX-50-2-7/111\_NH** for Bulk 100 pcs

<b>WAIVER!</b> While the information contained in this folder has been carefully compiled to the best of our present knowledge, it is not intended as representation or warranty of any kind on our part regarding the fitness of the products concerned for any particular use or purpose and neither shall any statement contained herein be constructed as a recommendation to infringe any industrial property rights or as a license to use any such rights. The fitness of each product for any particular purpose must be checked beforehand with our specialists.		 <b>HUBER+SUHNER</b> HUBER+SUHNER AG Interconnect Division CH-9100 Herisau Phone +41 (0)71 353 41 11 Fax +41 (0)71 353 45 90 <a href="http://www.hubersuhner.com">http://www.hubersuhner.com</a>
Issued: 18.12.03 08:51	Document: DOC-0000186531	
RF_Ca_Pa_C_PDF	<i>uncontrolled copy</i> Page 2	