



FED MFG CODE 91929

CATALOG LISTING

1 CH 28-4

BLACK  WHITE
GREEN

CIRCUIT DIAGRAM



3X CONDUCTOR CABLE TYPE SJO Δ 3

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

SCALE FULL

DO NOT SCALE PRINT

CHARACTERISTICS

ELECTRICAL DATA

CONTACT ARRANGEMENT

OPERATING FORCE-----6-12 LB.

S P D T

FULL OVERTRAVEL FORCE-----30 LB MAX

RELEASE FORCE-----4 LB MIN

PRETRAVEL. ----- 040 MAX

DIFFERENTIAL TRAVEL - - - - - 020 MAX

DIFFERENTIAL TRAVEL ----- 0.020 MAX
OVERTRAVEL ----- 250 MIN

OVERTRAVEL ----- 250 MIN

LOAD

LOAD

RES

RES
LND

IND
MOTOR

28 VDC

SEA LEVEL	50,000 FT.
-----------	------------

SEA LEVEL	50,000 FT.
4	4

$$\frac{4}{2} \quad \frac{4}{2}$$
$$\frac{2}{4}$$

REFERENCE UNLESS NOTED TOLERANCES ARE ±			
DIM		TOL	

	Step	Time/In	IN	Time/In
NO PLACES	K	1/84		
ONE PLACE	K X	0.4/018	2.2	0.2/003

ONE PLACE	XX	0 47/018	XX	0 87/03
TWO PLACES	XX	0 15/008	XX	0 38/01
THREE PLACES			XX	0 13/00
ANGLES				

ANGLES	SIMETRIC	US CUSTOMARY
--------	----------	--------------

DESIGN UNITS	☐	☒
--------------	--------------------------	-------------------------------------

RAW MATERIAL-COMMERCIAL STANDARD
M CRO SWITCH STANDARDS APPLY

DIMENSIONS ARE TO BE MET BEFORE PROTECTIVE COATINGS ARE APPLIED

WEIGHT 10 OZ MAX

NOTES

1 - SWITCH SEALED PER MIL-PRF-8805 SYMBOL 3

2 - CIRCUIT DIAGRAM, CATALOG LISTING, FED. MFG. CODE
AND DATE CODE ARE SHOWN ON NAMEPLATE

3 WIRE LEADS COLOR CODED TO SHOW LEAD IDENTIFICATION

4 HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-PRF-8805

[illegible]